

Article-No.	Dispenser and dosing systems	Skin Protection					Skin Cleansing					Skin care pr2000 + pr99
		pr88	pr88 liquid	pr99	prDH	prUV	prClean	prClean +	prClean R	prClean L	prClean D	
1088	pr88 Wall dispenser - stainless steel, for 1.6 litre dispenser cartridges	++										
1080	pr88 Wall dispenser - Macrolon plastic, to be filled from buckets ¹⁾	+										
1099	Wall dispenser - aluminium - lockable, for 1 litre bottles		++	++	++	++	++	++	○		++	++
1090	Wall dispenser - plastic, for 1 litre bottles		+	+	+	+	+	+			+	+
1010	Dosing pumps - 1 ml dosing volume for 1 litre bottles		○	+	+	+				2) +		+
1030	Dosing pumps - 3 ml dosing volume for 1 litre bottles						+	+	○		+	
1066	Wall brackets - stainless steel, for 1 litre bottles ³⁾		○	+	+	+	+	+	○	+	+	+
1200	Wall dispenser - metal, for 1 and 2 litre soft bottles			++	++	++	++	++	++		++	++
1250	Wall dispenser - plastic, for 1 and 2 litre soft bottles		++	++	++	++	++	++	++		++	++
1077	Wall dispenser - aluminium - lockable, for 2.5 litre bottles							++	++			
1070	Wall dispenser - plastic, for 2.5 litre bottles							+				
1040	Dosing pumps - no abrasives, for 2.5 litre bottles							+				
1042	Dosing pumps - abrasives, for 2.5 litre bottles							+	+			
1060	Wall brackets - stainless steel, for 2.5 litre bottles ³⁾							+	+			
1050	Dosing pumps - no abrasives, for 5 litre canisters						+	+				
1052	Dosing pumps - abrasives, for 5 litre canisters						+	+	+			
1065	Wall brackets - stainless steel, for 5 litre canisters ³⁾						+	+	+			
1100	Dosing pump with stainless steel lid, for 10 litre bucket prClean R								+			

The overview helps in selecting the appropriate dispenser and dosing systems for your application. We are happy to advise you personally - just call us at +49 25 97 / 96 24-0

Notes

- ++ very good combination, robust and durable - suitable for medium and large businesses / divisions
- + good combination - for small businesses / divisions suitable
- for small operators / departments, and suitable for private use

- 1) inexpensive dispenser with easy convenience - suitable for small operators / departments
- 2) due to the solvent contained in prClean L other donors are not suitable solutions for prClean L
- 3) viable option as a supplement to the screw-dosing